

TECHNICAL DATA

2x Telephoto Infrared Smart Lens RSE



Product overview: 2x Telephoto Infrared Smart Lens RSE

View your target magnified 2 times more than a standard lens, and reduce the need to enter the danger zone in your plant or to climb a tall ladder to capture the critical infrared details that could indicate your equipment has an issue.

Avoid the hassle of sending in your camera to calibrate with the lens — with smart lenses you can just attach the lens to any compatible camera and start taking images.

Made of 100% diamond-turned germanium with an engineered coating, the most efficient available material to transmit energy to the detector.

Compatible with RSE300, RSE600.

Specifications: 2x Telephoto Infrared Smart Lens RSE

| Description               |                             |           |
|---------------------------|-----------------------------|-----------|
| IFOV (spatial resolution) | RSE600                      | 0.47 mRad |
|                           | RSE300                      | 0.94 mRad |
| Field of view             | 12 ° H x 9 ° V              |           |
| Focus distance            | 45 cm (approximately 18 in) |           |

Fluke. *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Canada (800) 36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com](http://www.fluke.com)

©2024 Fluke Corporation.  
Specifications subject to change without notice.  
07/2024

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**